

# D16 Mechanical Anchor for Cryogenic Applications



The nVent LENTON brand of cryogenic reinforcement splicing systems should be specified whenever cryogenic-grade reinforcing bar is used, or during normal operating or emergency conditions where the temperature falls below -20 °C (-4 °F). By combining the nVent LENTON taper-threaded couplers with state-of-the-art materials, we have developed one of the slimmest couplers on the market, while still maintaining top performance. Typical construction projects include LNG and LPG storage tanks.

## FEATURES

Replaces conventional hooked reinforcing bar

Simplifies reinforcing bar placement and lowers placing costs

Head area exceeds 5x bar area (net 4x)

Improved performance and reliability at cryogenic temperatures (-168 °C / -270 °F)

## SPECIFICATIONS

**Finish:** Plain

**Material:** Stainless Steel 431 (EN 1.4057)

Table 1/1

| Catalog Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) | Unit Weight |
|----------------|--------------------|----------------|--------------------|--------------|------------|-------------|
| EL12D16CRN     | 12 mm              | #4             | 10M                | 35 mm        | 19mm       | 0.13 kg     |
| EL16D16CRN     | 16 mm              | #5             | 15M                | 36 mm        | 24mm       | 0.16 kg     |
| EL20D16CRN     | 20 mm              | #6             | 20M                | 45 mm        | 35mm       | 0.37 kg     |
| EL25D16CRN     | 25 mm              | #8             | 25M                | 60 mm        | 40mm       | 0.77 kg     |

| CatalogNumber | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) | Unit Weight |
|---------------|--------------------|----------------|--------------------|--------------|------------|-------------|
| EL28D16CRN    | 28 mm              | #9             | 30M                | 65 mm        | 42mm       | 0.94 kg     |
| EL32D16CRN    | 32 mm              | #10            |                    | 75 mm        | 46mm       | 1.35 kg     |

**Designed to Meet:** ACI 318;AS3600;ASTM A970;EN 14620-3

## ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Thread does not need to be flush with end of nVent LENTON Terminator. Thread may be +/- 2 threads from backside of coupler.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE