

MI Series Jacketed Copper Heating Cable



nVent RAYCHEM LSZH jacketed copper sheathed mineral insulated (MI) series resistance trace heating cables are used for low temperature maintenance applications including embedded heating in concrete or asphalt, roof de-icing, frost heave protection, exposed snow melting and interior pipe tracing. Continuous exposure temperatures to 194 °F/90 °C and typical power outputs to 35 W/ft (115 W/m depending on application.) Embedded and roof de-icing applications approved for use in hazardous areas.

FEATURES

Long circuit lengths possible enabling cost effective heating of large areas

Reduced power supply costs (lower start up currents compared with other technologies)

Three phase designs solutions allowing optimization of layouts

Red LSZH jacket aids visibility while pouring concrete or asphalt

Rugged cable construction

Reliable during long life, 10 year product warranty available (robust and rugged construction, proven in harsh climates extends life expectancy)

SPECIFICATIONS

Conductor Quantity:	1
Max Continuous Exposure Temperature, Power Off:	90 °C
Max Power Output:	115 W/m
Min Installation Temperature:	-30 °C
Sheath Material:	Copper
Area Classification:	Non-Hazardous; Hazardous
Insulation Material:	Magnesium Oxide

Table 1/1

Catalog Number	Supply Voltage	Conductor Material	Nominal Resistance @ 20°C	Outer Diameter
HCHR1L1250-RD	0 – 300 V	Copper Alloy	1250 Ω/km	5.1 mm

Catalog Number	Supply Voltage	Conductor Material	Nominal Resistance @ 20°C	Outer Diameter
HCHR1L2000-RD	0 – 300 V	Copper Alloy	2000 Ω/km	5.1 mm
HCHR1M100-RD	0 – 500 V	Copper Alloy	100 Ω/km	7.5 mm
HCHR1M140-RD	0 – 500 V	Copper Alloy	140 Ω/km	7.2 mm
HCHR1M1600-RD	0 – 500 V	Copper Alloy	1600 Ω/km	5.68 mm
HCHR1M220-RD	0 – 500 V	Copper Alloy	220 Ω/km	6.8 mm
HCHR1M315-RD	0 – 500 V	Copper Alloy	315 Ω/km	6.6 mm
HCHR1M630-RD	0 – 500 V	Copper Alloy	630 Ω/km	6.3 mm
HCHR1M800-RD	0 – 500 V	Copper Alloy	800 Ω/km	5.8 mm
HCCR1M11-RD	0 – 500 V	Copper	11 Ω/km	7.2 mm
HCCR1M17-RD	0 – 500 V	Copper	17 Ω/km	6.9 mm
HCCR1M25-RD	0 – 500 V	Copper	25 Ω/km	6 mm
HCCR1M4-RD	0 – 500 V	Copper	4 Ω/km	8.2 mm
HCCR1M40-RD	0 – 500 V	Copper	40 Ω/km	5.7 mm
HCCR1M7-RD	0 – 500 V	Copper	7 Ω/km	7.6 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT