

CompacPRO Rear Panel With Vented Slots



The rear panel with vented slots can be used for the CompacPRO case. The rear panel is bolted on the rear frame.

CERTIFICATIONS



FEATURES

Al material 3.0 mm

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized
Works With:	Cases
Product Family:	CompacPRO
Type:	Rear Panel
Product Type:	Side Panel

Table 1/1

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
30823-015	2U	42HP	1	No
30823-021	3U	28HP	1	No

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
30823-024	3U	42HP	1	No
30823-033	4U	42HP	1	No
30823-512	2U	84HP	1	No
30823-027	3U	63HP	1	No
30823-036	4U	63HP	1	No
30823-515	3U	84HP	1	No
30823-045	6U	63HP	1	No
30823-518	4U	84HP	1	No
30823-521	6U	84HP	1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE