

CPCI Serial Backplane



The nVent SCHROFF CompactPCI Serial backplanes support the highest data transfer rates with PCIe up to Gen 3, 10GbE, USB 3.0 and S-ATA Rev. 3.0

CERTIFICATIONS



FEATURES

Conforms to PICMG CompactPCI Serial (CPCI-S.0 R2.0) specification

Utility connector on rear of backplane

Mechanical centering and keying/coding strip in stainless steel on every fully equipped front and rear slot

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Number of Slots	Rack Height	Backplane Type	System Slot	Slot Width
23007-621	Backplane	1	3U	CompactPCI Serial, No Bus		4HP
23007-641	Backplane	1	3U	CompactPCI Serial, No Bus		4HP
23007-681	Backplane	1	3U	CompactPCI Serial, No Bus		4HP
23007-661	Backplane	1	3U	CompactPCI Serial, No Bus		4HP

CatalogNumber	Product Type	Number ofSlots	Rack Height	BackplaneType	System Slot	Slot Width
23007-642	Backplane	2	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-653	Backplane	3	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-682	Backplane	2	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-643	Backplane	3	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-654	Backplane	4	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-644	Backplane	4	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-683	Backplane	3	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-655	Backplane	5	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-645	Backplane	5	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-693	Backplane	3	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-636	Backplane	6	3U	CompactPCI Serial with Ethernet Star	Right	4HP

CatalogNumber	Product Type	Number ofSlots	Rack Height	BackplaneType	System Slot	Slot Width
23007-684	Backplane	4	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-694	Backplane	4	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-637	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-627	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-605	Backplane	5	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-695	Backplane	5	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP
23007-685	Backplane	5	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-629	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-628	Backplane	8	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-649	Backplane	9	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-639	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-676	Backplane	6	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-615	Backplane	5	3U	CompactPCI Serial with Ethernet Full- mesh	Right	4HP

CatalogNumber	Product Type	Number ofSlots	Rack Height	BackplaneType	System Slot	Slot Width
23007-677	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Right	4HP
23007-667	Backplane	7	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-668	Backplane	8	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-669	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Left	4HP
23007-689	Backplane	9	3U	CompactPCI Serial with Ethernet Full- mesh	Left	4HP
23007-679	Backplane	9	3U	CompactPCI Serial with Ethernet Star	Right	4HP

Table 2/2

Catalog Number	Connector Type	Power Connector Type	Utility Connector Type	Width	Package Quantity	Quick Ship
23007-621	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1	No
23007-641	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1	No
23007-681	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1	No
23007-661	AirMax VS	Microfit	MicroMatch, 10-pin	19.3mm	1	No
23007-642	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	19.3mm	1	No
23007-653	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1	No
23007-682	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	39.6mm	1	No
23007-643	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1	No

CatalogNumber	ConnectorType	Power ConnectorType	Utility ConnectorType	Width	Package Quantity	Quick Ship
23007-654	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1	No
23007-644	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1	No
23007-683	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1	No
23007-655	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1	No
23007-645	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1	No
23007-693	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	60mm	1	No
23007-636	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	120.9mm	1	No
23007-684	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1	No
23007-694	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	80.3mm	1	No
23007-637	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1	No
23007-627	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1	No
23007-605	AirMax VS	PwrBlade	MicroMatch, 10-pin	159.9mm	1	No
23007-695	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1	No
23007-685	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	100.6mm	1	No
23007-629	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1	No
23007-628	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	161.6mm	1	No
23007-649	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	191.9mm	1	No
23007-639	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1	No

CatalogNumber	ConnectorType	Power ConnectorType	Utility ConnectorType	Width	Package Quantity	Quick Ship
23007-676	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	120.9mm	1	No
23007-615	AirMax VS	PwrBlade	MicroMatch, 10-pin	159.9mm	1	No
23007-677	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1	No
23007-667	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	141.2mm	1	No
23007-668	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	161.6mm	1	No
23007-669	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1	No
23007-689	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1	No
23007-679	AirMax VS	Power Bugs for M4 Cable Lugs	MicroMatch, 10-pin	181.9mm	1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE