

# Varistar CP Cabeling Rack



Welded steel frame for high static load requirments.  
Prepared for high cable densities and 19" integration.

## FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

## SPECIFICATIONS

**Product Type:** Rack

**Material:** Steel

**Frame Material:** Steel

Table 1/3

| Catalog Number | Rack Height | Cladding Material | Frame Color | Height | Frame Color Code | Cladding Color |
|----------------|-------------|-------------------|-------------|--------|------------------|----------------|
| 10630-028      | 42U         | Steel             | Black Grey  | 2000mm | RAL 7021         | Black Grey     |
| 10630-027      | 42U         | Steel             | Black Grey  | 2000mm | RAL 7021         | Black Grey     |

Table 2/3

| Catalog Number | Width | Depth  | Static Load | Cladding Color Code | Package Quantity | Dynamic Load |
|----------------|-------|--------|-------------|---------------------|------------------|--------------|
| 10630-028      | 800mm | 1200mm | 1600kg      | RAL 7021            | 1                | 1000kgf      |
| 10630-027      | 800mm | 1200mm | 1600kg      | RAL 7021            | 1                | 1000kgf      |

Table 3/3

| Catalog Number | Finish        | Quick Ship |
|----------------|---------------|------------|
| 10630-028      | Powder Coated | No         |
| 10630-027      | Powder Coated | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**