

Varistar CP Steel Door, Plain With Multi-Point Locking, Shortened



IP55 Steel Door with lever handle and up to 4-Point locking (>2000mm).

FEATURES

Height of connection plate 400 mm

Connection plate can be assembled on top or bottom

Lever handle with push button

Opening angle 180°

Steel door with up to 4-point locking

SPECIFICATIONS

Product Type: Cabinet Door

Table 1/2

Catalog Number	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-372	38U	1800mm	600mm	IP55	1	
21630-373	38U	1800mm	800mm	IP55	1	
21630-374	42U	2000mm	600mm	IP55	1	
21630-375	42U	2000mm	800mm	IP55	1	

CatalogNumber	Rack Height	Height	Width	Protection Rating	Package Quantity	Color
21630-376	47U	2200mm	600mm	IP55	1	
21630-377	47U	2200mm	800mm	IP55	1	
21630-711	38U	1800mm	600mm	IP55	1	Black Grey
21630-712	38U	1800mm	800mm	IP55	1	Black Grey
21630-713	42U	2000mm	600mm	IP55	1	Black Grey
21630-714	42U	2000mm	800mm	IP55	1	Black Grey
21630-715	47U	2200mm	600mm	IP55	1	Black Grey
21630-716	47U	2200mm	800mm	IP55	1	Black Grey

Table 2/2					
Catalog Number	Color Code	Finish	Locking Type	Material	Quick Ship
21630-372		Powder Coated	3-Point Locking	Steel, Stainless Steel	No
21630-373		Powder Coated	3-Point Locking	Steel, Stainless Steel	No
21630-374		Powder Coated	4-Point Locking	Steel, Stainless Steel	No
21630-375		Powder Coated	4-Point Locking	Steel, Stainless Steel	No
21630-376		Powder Coated	4-Point Locking	Steel, Stainless Steel	No
21630-377		Powder Coated	4-Point Locking	Steel, Stainless Steel	No
21630-711	RAL 7021	Powder Coated	3-Point Locking	Steel	No
21630-712	RAL 7021	Powder Coated	3-Point Locking	Steel	No
21630-713	RAL 7021	Powder Coated	4-Point Locking	Steel	No

Catalog Number	Color Code	Finish	Locking Type	Material	Quick Ship
21630-714	RAL 7021	Powder Coated	4-Point Locking	Steel	No
21630-715	RAL 7021	Powder Coated	4-Point Locking	Steel	No
21630-716	RAL 7021	Powder Coated	4-Point Locking	Steel	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE