

CMP Mounting Plate



FEATURES

Used in conjunction with threaded rod

SPECIFICATIONS

Finish: Electrogalvanized

Table 1/1

Catalog Number	Rod Size	Length	Width	Thickness	Static Load
CMP12	12	100mm	25 mm	3 mm	4000N
CMP8	8	100mm	25 mm	3 mm	2500N
CMP10	10	100mm	25 mm	3 mm	3000N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

