

MACRO V Duct Clamp



FEATURES

Quick locking system for outer diameters up to 400 mm

Achieved noise reduction up to 16 dB(A) in controlled testing

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

SPECIFICATIONS

Finish: Electrogalvanized
Material: Steel;EPDM-SBR Rubber
Temperature: -50 to 110 °C


Table 1/2

Catalog Number	Article Number	Outer Diameter (OD)	Rod Size 1 (RS1)	Rod Size 2 (RS2)	Width (W)	Thickness (T)
MVI0300EG	582500	300 mm	8	10	23 mm	2 mm
MVI0250EG	582480	250 mm	8	10	23 mm	2 mm
MVI0355EG	582530	355 mm	8	10	23 mm	2 mm
MVI0280EG	582490	280 mm	8	10	23 mm	2 mm

CatalogNumber	Article Number	Outer Diameter (OD)	Rod Size 1 (RS1)	Rod Size 2 (RS2)	Width (W)	Thickness (T)
MVI0224EG	582470	224 mm	8	10	23 mm	2 mm

Table 2/2				
Catalog Number	Article Number	Screw Diameter (Sc)	Screw Length (L)	Static Load
MVI0300EG	582500	6	40mm	750N
MVI0250EG	582480	6	40mm	750N
MVI0355EG	582530	6	40mm	750N
MVI0280EG	582490	6	40mm	750N
MVI0224EG	582470	6	40mm	750N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

