

Metal Pressure Clip with Nail Gun Insert



FEATURES

Clips onto nozzle of gas or battery-actuated nail guns allowing for hands-off installation at structure or from the floor using a pole

Ideal for smaller runs of cables

Flexible clip retains shape and allows for cables to be inserted after installation

Rounded edges help prevent cable damage

Cables are neatly installed providing a consistent and professional appearance

Low profile allows for installations in tight spaces

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel;Nylon

Table 1/1

Catalog Number	Article Number	Cable Capacity	Diameter (Ø)	Hole Size (HS)	Length (L)
PKM16H3GBSF	182054	16	10 mm	3 mm	233.5mm
PKM10H3GBSF	182053	10	10 mm	3 mm	171.5mm

ADDITIONAL PRODUCT DETAILS

Supports cable diameters up to 1/2" (13 mm) when installed with a standard 1/4" (6 mm) washer.

Nail gun insert is compatible with BeA® CN60-688ES, Hilti® BX 3, GX 3, DEWALT® Trak-It C3, SPIT® PULSA 40E, 800E, 700, 1000 or equivalent nailers.

Please consult with the nail manufacturer to evaluate the static load of the nail and type of concrete used for the installation.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

