

IceStop Self-Regulating Heating Cable

Data Solutions



nVent RAYCHEM IceStop self-regulating trace heating cables provide roof and gutter de-icing, suitable for all standard materials of gutters and drainpipes. Power output is 36 W/m at 0 °C in ice water, 18 W/m at 0 °C in air.

FEATURES

Simple to design

Easy to install: cut to length, meter marks, simple fast RayClic connections

Safe and efficient in operation: no overheating, even when crossed, advanced energy saving controls

Reliable during long life: 10 year extended product warranty available, maintenance free

GM-2XT for bitumen roofs

SPECIFICATIONS

Nominal Thickness:	6mm
Nominal Width:	14mm
Nominal Cable Weight:	130g/m
Min Installation Temperature:	-18°C
Color:	Black
Ground Path Type:	Braid
Conductor Material:	Nickel-Plated Copper

Table 1/1

Catalog Number	Article Number	Supply Voltage	Nominal Power Output, In Air @ 0°C, 230V	Nominal Power Output, In Ice Water @ 0°C, 230V	Outer Jacket Material
----------------	----------------	----------------	--	--	-----------------------

092961-000	GM-2XT	208 – 240V	18W/m	36W/m	Fluoropolymer
446105-000	GM-2X	208 – 240V	18W/m	36W/m	Modified Polyolefin
832100-000	GM-1X	120V			Modified Polyolefin
900069-000	GM-1XT	120V			Fluoropolymer

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE