

Varistar CP Air Separation Blanking Cover, Width 800 mm, With Brush Strip and Fingers

Data Solutions



Filler panel for 800 mm wide cabinets to avoid air recirculation in front to back cooled racks. Plain panels and panels with cutouts for front to back cabling with brush stripes and cable fingers.

FEATURES

Air separation, covers for 800 mm wide cabinets

Network and server cabinets can be arranged side by side

Gaskets, UL 94 HF-1, -20 °C ... 100° C

Cover with cutouts and cable fingers for efficient cable management

Brush strips available to close the cutouts

Covers prevent unwanted air short-circuits, i.e. unwanted mixing of warm exhaust air with cold inbound air

Only compatible with heavy load crossbar, not compatible with reduction brackets

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Material: Steel

Table 1/2

Catalog Number	Rack Height	Height	Package Quantity	Color	Color Code	Finish
21630-150	42U	2000mm	1	Black Grey	RAL 7021	Powder Coated
21630-152	52U	2450mm	1	Black Grey	RAL 7021	Powder Coated

CatalogNumber	Rack Height	Height	Package Quantity	Color	Color Code	Finish
21630-151	47U	2200mm	1	Black Grey	RAL 7021	Powder Coated

Table 2/2

Catalog Number	Protection Rating	Type	Width
21630-150	IP20	Cable Duct	800mm
21630-152	IP20	Cable Duct	800mm
21630-151	IP20	Cable Duct	800mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE