

Denso Tape



FEATURES

Cold applied tape for the protection of pipes, complex objects and all buried metal structures

Designed for surfaces that are subject to exposure of high operating temperatures

SPECIFICATIONS

Material: Synthetic Fibre Temperature: 115 °C Max

Table 1/1 **Catalog Number Article Number** Length Width **Thickness Unit Weight** DENSOTAPE 10m 711520 50 mm 1.4 mm 0.76 kg DENSO-100-10 10m 100 mm 1.4 mm 1.5 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE