

Heat Shrink Insulation, Straight



FEATURES

Heat shrink tubing for insulating connections

SPECIFICATIONS

Conductor Size, UL:	0.35" - 0.94"
Shrink Ratio:	4:1
Color:	Black
Material:	Polyolefin

Table 1/1

Catalog Number	Expanded Diameter	Recovered Diameter	Length (L)	Diameter (Ø)	Dielectric Strength	Temperature
A130AEWTB01	33.27 mm Min	8 mm Max	152.4mm	38.1 mm	430	-18 to 90 °C
A130AE	33.27 mm Min	8 mm Max	1219.2mm	38.1 mm	430	-18 to 90 °C

ADDITIONAL PRODUCT DETAILS

Recovered Diameter refers to the final inner diameter of the tubing after the tubing has been fully shrunk, or recovered, through the careful application of heat. A maximum value is specified to ensure the tubing will fit tightly around the object being covered.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE