

# nVent ERICO Ericontact Insertion Tool, Manual



## FEATURES

Used to insert single and double nVent ERICO Ericontact Rail Contacts

Packaged in a toolbox for safe and convenient handling

Includes two MDRL (715215) Mandrels for 19 mm nVent ERICO Ericontact

## SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Applied Force | Operating Pressure | System                                               |
|----------------|----------------|---------------|--------------------|------------------------------------------------------|
| HSKE           | 715345         | 57kN          | 630bar             | Hydraulic head with manually-operated hydraulic pump |

## ADDITIONAL PRODUCT DETAILS

Kit includes: (2) mandrels for 19 mm nVent ERICO Ericontact rail contact, (1) deburr tool, (1) test gauge, (1) metal case, (1) HSKE pump connected with a high pressure hydraulic hose to the PSKE unit, and (1) manual HSKE.

| ERICO ERICONTACT Rail Contact Size | Required Parts                                                   |                  |
|------------------------------------|------------------------------------------------------------------|------------------|
| 8 mm                               | MDRL8ADP (715218) Mandrel Adaptor and MDRL8 (715216) Mandrel     | Order separately |
| 13.5 mm                            | MDRL135ADP (715219) Mandrel Adaptor and MDRL135 (715217) Mandrel | Order separately |
| 19 mm                              | MDRL (715215) Mandrel                                            | Included         |
| 22 mm                              | PSKECMB (715596) Insertion Head Plate                            | Order separately |

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**