nVent | ERICO

We connect and protect

SB/SBL Hollow Core Rail Drill Bit

FEATURES

- Designed for high-speed drilling applications
- Withstands approximately 40 uses
- Can be reground for further use
- Specifically developed for rail steel
- 3/4" (19 mm) Weldon shank
- Allows for short drill times
- High durability provides extended lifetime

SPECIFICATIONS

Material: High-Speed Steel

Finish: TIALN Coating

Table 1/1

Catalog Number	Article Number	Drill Bit Diameter (Ø)	Length (L)
DHC36	716498	36 mm	63mm
DHC35	716497	35 mm	63mm
DHC18	716492	18 mm	63mm
DHC27	716496	27 mm	63mm

Catalog Number	Article Number	Drill Bit Diameter (Ø)	Length (L)
DHC25	716495	25 mm	63mm
DHC19	716493	19 mm	63mm
DHC23	716494	23 mm	63mm
DSB1670	715251	16 mm	70mm
DSB1770	715252	17 mm	70mm
DSB2270	715255	22 mm	70mm
DSBL1690	716301	16 mm	90mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.