

Stainless Steel Ground Rod, Threaded



CERTIFICATIONS



FEATURES

Utilizes a cut thread for highly corrosive soil

SPECIFICATIONS

Tensile Strength: 483 MPa Min


Table 1/2

Catalog Number	Material	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)	Length (L)	Unit Weight
685800S	Stainless Steel 304 (EN 1.4301)	5/8"	16 mm	5/8" UNC	3.05mm	4.7 kg
685880S	Stainless Steel 304 (EN 1.4301)	5/8"	16 mm	5/8" UNC	2.44mm	3.5 kg
683400S	Stainless Steel 304 (EN 1.4301)	3/4"	19.1 mm	3/4" UNC	3.05mm	6.8 kg

CatalogNumber	Material	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)	Length (L)	Unit Weight
683450S	Stainless Steel 304 (EN 1.4301)	3/4"	19.1 mm	3/4" UNC	1.52mm	3.1 kg
683400S316	Stainless Steel 316 (EN 1.4401)	3/4"	19.1 mm	3/4" UNC	3000mm	6.3 kg
684400S	Stainless Steel 304 (EN 1.4301)	1"	25.4 mm	1" UNC	3.05mm	12.1 kg

Table 2/2	
Catalog Number	Certifications
685800S	UL, cUL
685880S	UL, RUS
683400S	cUL, UL
683450S	
683400S316	UL, cUL
684400S	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE