

Tape Clamp



FEATURES

Secures lightning protection conductors and prevents displacement

Mechanically secured with screws or nails

SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	Material	Tape Size	Tape Type	Depth (D)	Height (H)
DCA600	711760	Aluminum	25 x 3 mm	Insulated	20mm	13 mm
DCC316	711660	Brass	31 x 6 mm	Bare	18mm	13 mm
DCC256	711230	Brass	25 x 6 mm	Bare	20mm	14 mm
DCC605	711260	Brass	25 x 6 mm	Insulated	20mm	15 mm
DCC386	711690	Brass	38 x 6 mm	Bare	20mm	13 mm
DCC506	711240	Brass	50 x 6 mm	Bare	20mm	13 mm
DCC610	711270	Brass	50 x 6 mm	Insulated	20mm	15 mm

Table 2/2

Catalog Number	Article Number	Width (W)	Hole Size (HS)	Unit Weight
DCA600	711760	52 mm	7 mm	0.04 kg
DCC316	711660	56 mm	7 mm	0.067 kg
DCC256	711230	50 mm	7 mm	0.08 kg
DCC605	711260	52 mm	7 mm	0.13 kg
DCC386	711690	63 mm	7 mm	0.14 kg
DCC506	711240	75 mm	7 mm	0.16 kg
DCC610	711270	78 mm	7 mm	0.26 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE