

Universal Conductor Clamp with Adhesive Base



FEATURES

For use on flat roof surfaces

Base can be placed in gravel or secured using adhesive

Secures either round or tape conductors

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Conductor Size	Tape Size	Diameter (Ø)	Height (H)
SFRRSFT65	106310	Nylon	6 mm Solid - 11 mm Solid	25 x 3 mm, 26 x 2 mm, 30 x 2 mm	110 mm	65 mm

Table 2/2

Catalog Number	Article Number	Unit Weight
SFRRSFT65	106310	0.03 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE