

FRCB Flat Braid in Coil, Plain Copper



CERTIFICATIONS



FEATURES

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

SPECIFICATIONS

Material: Copper

Table 1/2

Catalog Number	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
FRCB15-10	557030	75A	10mm ²	576	0.15mm	25m
FRCB15-100	557150	360A	100mm ²	5664	0.15mm	25m
FRCB15-16	557040	120A	16mm ²	896	0.15mm	25m
FRCB15-25	557060	150A	25mm ²	1404	0.	

CatalogNumber	Article Number	Nominal Current	Cross Section	Number of Wires	Wire Diameter	Length
FRCB15-35	557080	200A	35mm ²	1980	0.15mm	25m
FRCB15-40	557090	220A	40mm ²	2272	0.15mm	25m
FRCB15-50	557100	250A	50mm ²	2848	0.15mm	25m
FRCB15-75	557130	300A	75mm ²	4256	0.15mm	25m

Table 2/2

Catalog Number	Article Number	Thickness	Width	Unit Weight
FRCB15-10	557030	1.5 mm	10 mm	0.1 kg
FRCB15-100	557150	4 mm	40 mm	1 kg
FRCB15-16	557040	1.5 mm	15 mm	0.16 kg
FRCB15-25	557060	1.5 mm	23 mm	0.25 kg
FRCB15-35	557080	2.5 mm	23 mm	0.35 kg
FRCB15-40	557090	2.5 mm	25 mm	0.4 kg
FRCB15-50	557100	3 mm	28 mm	0.5 kg
FRCB15-75	557130	4 mm	30 mm	0.75 kg

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY