

# MFBT-2 nVent ERIFLEX Flexibar Manual Bending Tool



## CERTIFICATIONS



## FEATURES

Allows the user to bend nVent ERIFLEX Flexibar into custom shapes for an efficient installation

Easy-to-use tool bends all sizes of nVent ERIFLEX Flexibar quickly without damage to the insulation

Long handle to apply force during nVent ERIFLEX Flexibar bending up to 10x120x1/12x100x1

Bending radius: 5 mm (0.20")

Allows for adjustment of the bending angle for repetitive bending

Robust blue aluminum base with three fixing points

Adjustable length setting for nVent ERIFLEX Flexibar

Quick nVent ERIFLEX Flexibar locking system with no tools required

RoHS compliant

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Conductor Width | Bending Radius | Bending Angle | Depth |
|----------------|----------------|----------|-----------------|----------------|---------------|-------|
|----------------|----------------|----------|-----------------|----------------|---------------|-------|

|        |        |                    |        |     |           |       |
|--------|--------|--------------------|--------|-----|-----------|-------|
| MFBT-2 | 559145 | Steel,<br>Aluminum | 120 mm | 5mm | 120 ° Max | 414mm |
|--------|--------|--------------------|--------|-----|-----------|-------|

Table 2/2

| Catalog Number | Article Number | Height | Width  | Unit Weight |
|----------------|----------------|--------|--------|-------------|
| MFBT-2         | 559145         | 242 mm | 319 mm | 7 kg        |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE