

Cable Entry Gland Plate Round, CEPR



Quick and easy to install without tools, CEPRL round cable entries are ideally suited for applications that require many incoming or outgoing cables and have limited installation space.

INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12; File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12

CE

IP54

FEATURES

Finish: Gray

Pack quantity: 10

Description: Quick and easy to install without tools, round cable entries are ideally suited for applications that require many incoming or outgoing cables or pneumatic conduits inside an enclosure. The snap-in system is designed for wall thicknesses of 1.5 to 2.5 mm.

Temperature resistance: -40°C to +90°C

Flammability: UL94 V-0

Protection: IP54, NEMA 1, 12 (indoor use only)

Material: TPE

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Cable Entry Quantity	Cable Entry	Cutout Size	Height	Width
CEPRL5009	58286	9	(5) 1.0 - 7.0 mm, (4) 1.0 - 18.0 mm	50 Ømm	58mm	58mm
CEPRL5018	58292	18	(2) 1.0 - 4.0 mm, (2) 1.0 - 6.0 mm, (4) 1.0 - 7.2 mm, (5) 1.0 - 9.4 mm, (5) 1.0 - 12.0 mm	50 Ømm	58mm	58mm
CEPRL5011	58287	11	(7) 1.0 - 7.2 mm, (3) 1.0 - 11.2 mm, (1) 1.0 - 22.5 mm	50 Ømm	58mm	58mm
CEPRL5012	58288	12	(10) 1.0 - 9.2 mm, (2) 1.0 - 11.2 mm	50 Ømm	58mm	58mm
CEPRL5016	58289	16	(4) 1.0 - 5.3 mm, (5) 1.0 - 6.3 mm, (3) 1.0 - 9.5 mm, (4) 1.0 - 11.3 mm	50 Ømm	58mm	58mm
CEPRL5020	58293	20	(16) 1.0 - 6.3 mm, (4) 1.0 - 9.3 mm	50 Ømm	58mm	58mm
CEPRL5035	58294	35	(35) 1.0 - 5.2 mm	50 Ømm	58mm	58mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE