

Inner Doors For Power Distribution, DI, 1953x565x53mm, Light Gray, Mild Steel

CATALOG NUMBER

DI2006R5



Displays and indicators can be mounted on a surface within the enclosure while covering other components, and preventing unauthorized access.

FEATURES

Description: Inner door provides a hinged mounting surface for equipment behind a standard or glazed front door. A mounting space of 80 mm, is available between the doors when the inner door is in the most forward position. Can be adjusted in depth by steps of 25 mm. The mounting plate remains usable behind the inner door. The door is equipped with two double-bit 3 mm locks.

Material: 1.5 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 door with mounting accessories.

PRODUCT ATTRIBUTES

Article Number: DI2006R5

Height: 1953mm

Width: 565mm

Depth: 53mm

Enclosure Material: Mild Steel

Product Family: Free-Standing

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 1.5mm

Package Quantity: 1

Weight: 23.8kg

ADDITIONAL PRODUCT DETAILS

Other sizes available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE