

## FS66S Plinth Base

Plinth bases install under an enclosure to provide space for cables to enter from below for type FM FS66S.



### FEATURES

---

1 set for each, consisting of:

2X channel supports on left and right

2X plinth covers for front and rear

All necessary mounting hardware is included

## SPECIFICATIONS

Table 1/1

| Catalog Number | Material            | Finish  | Thickness | Fits Enclosure Width | Fits Enclosure Depth | Quick Ship |
|----------------|---------------------|---------|-----------|----------------------|----------------------|------------|
| FMPL0604S010S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 400mm                | No         |
| FMPL0604S020S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 400mm                | No         |
| FMPL0604S030S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 400mm                | No         |
| FMPL0605S010S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 500mm                | No         |
| FMPL0605S020S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 500mm                | No         |
| FMPL0605S030S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 500mm                | No         |
| FMPL0606S010S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 600mm                | No         |
| FMPL0606S020S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 600mm                | No         |
| FMPL0606S030S  | Stainless Steel 304 | Brushed | 2mm       | 600mm                | 600mm                | No         |
| FMPL0806S010S  | Stainless Steel 304 | Brushed | 2mm       | 800mm                | 600mm                | No         |
| FMPL0806S020S  | Stainless Steel 304 | Brushed | 2mm       | 800mm                | 600mm                | No         |
| FMPL0806S030S  | Stainless Steel 304 | Brushed | 2mm       | 800mm                | 600mm                | No         |
| FMPL0808S010S  | Stainless Steel 304 | Brushed | 2mm       | 800mm                | 800mm                | No         |
| FMPL0808S020S  | Stainless Steel 304 | Brushed | 2mm       | 800mm                | 800mm                | No         |
| FMPL0808S030S  | Stainless Steel 304 | Brushed | 2mm       | 800mm                | 800mm                | No         |
| FMPL1005S010S  | Stainless Steel 304 | Brushed | 2mm       | 1000mm               | 500mm                | No         |
| FMPL1005S020S  | Stainless Steel 304 | Brushed | 2mm       | 1000mm               | 500mm                | No         |
| FMPL1005S030S  | Stainless Steel 304 | Brushed | 2mm       | 1000mm               | 500mm                | No         |

| Catalog Number | Material            | Finish  | Thickness | Fits Enclosure Width | Fits Enclosure Depth | Quick Ship |
|----------------|---------------------|---------|-----------|----------------------|----------------------|------------|
| FMPL1006S010S  | Stainless Steel 304 | Brushed | 2mm       | 1000mm               | 600mm                | No         |
| FMPL1006S020S  | Stainless Steel 304 | Brushed | 2mm       | 1000mm               | 600mm                | No         |
| FMPL1006S030S  | Stainless Steel 304 | Brushed | 2mm       | 1000mm               | 600mm                | No         |
| FMPL1204S010S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 400mm                | No         |
| FMPL1204S020S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 400mm                | No         |
| FMPL1204S030S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 400mm                | No         |
| FMPL1205S010S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 500mm                | No         |
| FMPL1205S020S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 500mm                | No         |
| FMPL1205S030S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 500mm                | No         |
| FMPL1206S010S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 600mm                | No         |
| FMPL1206S020S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 600mm                | No         |
| FMPL1206S030S  | Stainless Steel 304 | Brushed | 2mm       | 1200mm               | 600mm                | No         |
| FMPL1406S010S  | Stainless Steel 304 | Brushed | 2mm       | 1400mm               | 600mm                | No         |
| FMPL1406S020S  | Stainless Steel 304 | Brushed | 2mm       | 1400mm               | 600mm                | No         |
| FMPL1406S030S  | Stainless Steel 304 | Brushed | 2mm       | 1400mm               | 600mm                | No         |
| FMPL1606S010S  | Stainless Steel 304 | Brushed | 2mm       | 1600mm               | 600mm                | No         |
| FMPL1606S020S  | Stainless Steel 304 | Brushed | 2mm       | 1600mm               | 600mm                | No         |
| FMPL1606S030S  | Stainless Steel 304 | Brushed | 2mm       | 1600mm               | 600mm                | No         |
| FMPL1608S010S  | Stainless Steel 304 | Brushed | 2mm       | 1600mm               | 800mm                | No         |
| FMPL1608S020S  | Stainless Steel 304 | Brushed | 2mm       | 1600mm               | 800mm                | No         |

| Catalog Number | Material            | Finish        | Thickness | Fits Enclosure Width | Fits Enclosure Depth | Quick Ship |
|----------------|---------------------|---------------|-----------|----------------------|----------------------|------------|
| FMPL1608S030S  | Stainless Steel 304 | Brushed       | 2mm       | 1600mm               | 800mm                | No         |
| FMPL1910S010S  | Stainless Steel 304 | Brushed       | 2mm       | 1900mm               | 1000mm               | No         |
| FMPL1910S020S  | Stainless Steel 304 | Brushed       | 2mm       | 1900mm               | 1000mm               | No         |
| FMPL1910S030S  | Stainless Steel 304 | Brushed       | 2mm       | 1900mm               | 1000mm               | No         |
| FMPL4010S010S  | Stainless Steel 304 | Brushed       | 2mm       | 4000mm               | 1000mm               | No         |
| FMPL4010S020S  | Stainless Steel 304 | Brushed       | 2mm       | 4000mm               | 1000mm               | No         |
| FMPL4010S030S  | Stainless Steel 304 | Powder Coated | 2mm       | 4000mm               | 1000mm               | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE