

Outer Mounting Profiles, CLPO



A standard, off the shelf accessory compatible with nVent HOFFMAN's standard hole pattern, which simplifies procurement and installation.

FEATURES

Description: Universal profile for both depth and width fitting on the 25 mm DIN hole pattern on the enclosure frame. The 75 mm wide profile is equipped with three rows of holes of which one is turned 90°. This makes it possible to mount the CLPO profiles in both directions. The CLPO increases the useful space by 25 mm.

Material: 1.5 mm zinc plated steel.

Pack quantity: 4 profiles.

SPECIFICATIONS

Thickness: 1.5mm
Finish: Galvanized
Material: Mild Steel

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Load Rating	Enclosure Material
CLPO1000	CLPO1000	74mm	43mm	911mm	1400N	Mild Steel
CLPO1200	CLPO1200	74mm	43mm	1111mm	1200N	Mild Steel
CLPO400	CLPO400	74mm	43mm	311mm	2400N	Mild Steel
CLPO500	CLPO500	74mm	43mm	411mm	2400N	Mild Steel
CLPO600	CLPO600	74mm	43mm	511mm	2400N	Mild Steel
CLPO800	CLPO800	74mm	43mm	711mm	1800N	Mild Steel
CLPO300		74mm	43mm	211mm	2400N	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE