

Interscale 19" Rack Mount Chassis, Perforated

Power Utilities



Flexible 19" Chassis with integrated EMC protection and perforated side. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

CERTIFICATIONS



FEATURES

Modular desktop case consisting of 4 assembled parts, with perforated sides

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Depth	Package Quantity	Usable Width	Mounting	Complies With
14826-105	1 U	221 mm	1	444 mm	Rack	IEC 60297-3-100

CatalogNumber	Rack Height	Depth	Package Quantity	Usable Width	Mounting	Complies With
14826-107	1 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-307	3 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-205	2 U	221 mm	1	444 mm	Rack	IEC 60297-3-100
14826-207	2 U	310 mm	1	444 mm	Rack	IEC 60297-3-100
14826-305	3 U	221 mm	1	444 mm	Rack	IEC 60297-3-100

Table 2/2

Catalog Number	EMC Shielding	Product Family	Product Type	Type
14826-105	Yes	Interscale	Small Form Factor Case	Perforated
14826-107	Yes	Interscale	Small Form Factor Case	Perforated
14826-307	Yes	Interscale	Small Form Factor Case	Perforated
14826-205	Yes	Interscale	Small Form Factor Case	Perforated
14826-207	Yes	Interscale	Small Form Factor Case	Perforated
14826-305	Yes	Interscale	Small Form Factor Case	Perforated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE