

Varistar CP Mobile Base/Plinth

Power Utilities

Mobile base/plinth to make a cabinet mobile.

FEATURES

Covers, St, 1.5 mm

Load-carrying capacity on casters 400 kg, on adjustable feet 1000 kg

Support, St, 3 mm

Color RAL 7021

Plinth height H = 103 mm, with feet adjustable from 126 to 134 mm

SPECIFICATIONS

Table 1/2

Catalog Number	Width	Depth	Color	Color Code	Product Type	Type
21630-658	600 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-655	600 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-657	600 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-656	600 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-661	800 mm	600 mm			Cabinet/Rack Base	Base Plinth, Mobile
21630-663	800 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile
21630-664	800 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile

CatalogNumber	Width	Depth	Color	Color Code	Product Type	Type
21630-662	800 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Base	Base Plinth, Mobile

Table 2/2

Catalog Number	Works With
21630-658	Varistar CP
21630-655	Varistar CP
21630-657	Varistar CP
21630-656	Varistar CP
21630-661	Varistar CP
21630-663	Varistar CP
21630-664	Varistar CP
21630-662	Varistar CP

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE