

# Air Baffle, Front Panel, Retrofit Shielding, Steel



The air baffle with flat front panel covers an empty slot and eliminates an air leak. The flat front panel accepts a stainless steel EMC gasket.

## CERTIFICATIONS



## FEATURES

Air baffle eliminates air leaks from empty slots

Cover is pushed into the guide rail

## SPECIFICATIONS

|                        |                                                                       |
|------------------------|-----------------------------------------------------------------------|
| <b>Product Type:</b>   | Air Baffle                                                            |
| <b>Material:</b>       | Aluminum                                                              |
| <b>Finish:</b>         | Anodized; Passivated                                                  |
| <b>Product Family:</b> | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac |
| <b>Type:</b>           | With Front Panel                                                      |

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Depth | EMC Shielding      | Rack Width | Works With      |
|----------------|-------------|------------------|-------|--------------------|------------|-----------------|
| 20848-712      | 3U          | 1                | 160mm | No (Retrofittable) | 4HP        | Subracks, Cases |

| CatalogNumber | Rack Height | Package Quantity | Depth | EMC Shielding      | Rack Width | Works With      |
|---------------|-------------|------------------|-------|--------------------|------------|-----------------|
| 20848-721     | 6U          | 1                | 220mm | No (Retrofittable) | 4HP        | Subracks, Cases |
| 20848-720     | 6U          | 1                | 160mm | No (Retrofittable) | 4HP        | Subracks, Cases |
| 20848-713     | 3U          | 1                | 220mm | No (Retrofittable) | 4HP        | Subracks, Cases |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 20848-712      | No         |
| 20848-721      | No         |
| 20848-720      | No         |
| 20848-713      | No         |

## ADDITIONAL PRODUCT DETAILS

Air baffle for 280 mm deep and for 80 mm rear I/O boards available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**