

PropacPRO Complete Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

CERTIFICATIONS



FEATURES

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Unshielded

Ventilation slots in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

SPECIFICATIONS

Static Load:	25kg
Product Type:	Case
Type:	Case for 19" Components
EMC Shielding:	No (Retrofittable)
Product Family:	PropacPRO

Table 1/3

Catalog Number	Rack Height	Rack Width	Depth	Package Quantity	Usable Height	Usable Width
24576-013	3U	84HP	506mm	1	112.3mm	432mm
24576-010	3U	84HP	326mm	1	112.3mm	432mm
24576-011	3U	84HP	386mm	1	112.3mm	432mm
24576-002	3U	28HP	326mm	1	112.3mm	148mm
24576-009	3U	84HP	266mm	1	112.3mm	432mm
24576-008	3U	63HP	386mm	1	112.3mm	326mm
24576-012	3U	84HP	446mm	1	112.3mm	432mm
24576-007	3U	63HP	326mm	1	112.3mm	326mm
24576-003	3U	42HP	266mm	1	112.3mm	219mm
24576-006	3U	63HP	266mm	1	112.3mm	326mm
24576-021	6U	84HP	326mm	1	245.7mm	432mm
24576-001	3U	28HP	266mm	1	112.3mm	148mm
24576-004	3U	42HP	326mm	1	112.3mm	219mm
24576-005	3U	42HP	386mm	1	112.3mm	219mm
24576-022	6U	84HP	446mm	1	245.7mm	432mm

Table 2/3

Catalog Number	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-013	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum

CatalogNumber	Front Frame Construction	Cooling Option	Complies With	Finish	Height	Material
24576-010	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-011	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-002	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-009	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-008	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-012	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-007	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-003	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-006	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-021	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	289mm	Aluminum
24576-001	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-004	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-005	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	155.5mm	Aluminum
24576-022	Single Piece	No	IEC 60297-3-101	Passivated, Powder Coated	289mm	Aluminum

Table 3/3

Catalog Number	Protection Rating	Width	Quick Ship
24576-013	IP20	470.3mm	No
24576-010	IP20	470.3mm	No
24576-011	IP20	470.3mm	No

Catalog Number	Protection Rating	Width	Quick Ship
24576-002	IP20	185.9mm	No
24576-009	IP20	470.3mm	No
24576-008	IP20	363.7mm	No
24576-012	IP20	470.3mm	No
24576-007	IP20	363.7mm	No
24576-003	IP20	257mm	No
24576-006	IP20	363.7mm	No
24576-021	IP20	470.3mm	No
24576-001	IP20	185.9mm	No
24576-004	IP20	257mm	No
24576-005	IP20	257mm	No
24576-022	IP20	470.3mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE