

PropacPRO EMC Rear Panel, Full Width



The EMC rear panel, full width for PropacPRO Case mounts to the frame of the case. It has no perforation. The shielding is done with textile EMC gaskets.

CERTIFICATIONS



FEATURES

Alu panel, 1.5 mm, with fastener for Earthing / GND

Mounts on case (left, right)

Without perforation

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
Works With:	Cases
Product Family:	PropacPRO
Type:	Rear Panel
Product Type:	Side Panel

Table 1/1

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
24576-244	2U	42HP	1	No
24576-247	3U	28HP	1	No

Catalog Number	Rack Height	Rack Width	Package Quantity	Quick Ship
24576-248	3U	42HP	1	No
24576-245	2U	63HP	1	No
24576-252	4U	42HP	1	No
24576-249	3U	63HP	1	No
24576-250	3U	84HP	1	No
24576-253	4U	63HP	1	No
24576-254	4U	84HP	1	No
24576-258	6U	84HP	1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE