

# Varistar CP Plain Steel Door, Seismic IP55, With Multi-Point Locking



IP55 Seismic Steel Door with lever handle and multi-Point locking.

## FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for EMC applications

## SPECIFICATIONS

**Product Type:** Cabinet Door

**Protection Rating:** IP55

**Material:** Steel

Table 1/3

Catalog Number	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-752	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-753	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-754	38U	600mm	600mm	1	Black Grey	RAL 7021
21630-755	38U	1800mm	800mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-756	42U	2000mm	600mm	1	Black Grey	RAL 7021
21630-757	42U	2000mm	800mm	1	Black Grey	RAL 7021
21630-758	47U	2200mm	600mm	1	Black Grey	RAL 7021
21630-759	47U	2200mm	800mm	1	Black Grey	RAL 7021

Table 2/3

Catalog Number	Complies With	Finish	Locking Type	Rack Width	Type	Works With
21630-752	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Steel Door, Plain	Varistar CP
21630-753	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking	800HP	Steel Door, Plain	Varistar CP
21630-754	IEC 61587-2, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Steel Door, Plain	Varistar CP
21630-755	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Steel Door, Plain	Varistar CP
21630-756	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Steel Door, Plain	Varistar CP
21630-757	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	4-Point Locking		Steel Door, Plain	Varistar CP
21630-758	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	5-Point Locking		Steel Door, Plain	Varistar CP
21630-759	IEC 61587-1, IEC 61587-2, IEC 60529	Powder Coated	5-Point Locking		Steel Door, Plain	Varistar CP

Table 3/3

Catalog Number	Quick Ship
21630-752	No

Catalog Number	Quick Ship
21630-753	No
21630-754	No
21630-755	No
21630-756	No
21630-757	No
21630-758	No
21630-759	No

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**