

nVent CADDY Speed Link SLK with Y-Toggle



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and two pre-assembled toggle end fittings

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

SPECIFICATIONS

Wire Rope Diameter:	1.5 mm
Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Material:	Steel;Zinc Alloy;Polypropylene
Complies With:	SMACNA HVAC-DCS


Table 1/1

Catalog Number	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B	Static Load
SLK15Y300L3R 2	196648	3m	0.3m	39 mm	5 mm	195N

CatalogNumber	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B	Static Load
SLK15Y500L3	196528	3m	0.5m	39 mm	5 mm	195N

Thickness (T): 12.5 mm
Width (W): 19 mm
Height (H): 55 mm
Angle (a): 90 ° Max

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

