

Ground Mounted Plinth, PGM



Cables can be easily routed through the ground plinth, which is mounted underground, allowing cables to be channelled and therefore, wired more quickly.

FEATURES

Description: Ground mounted plinth 1000 mm height. Excavation depth: 700-950 mm.

Material: 2 mm galvanized steel.

Finish: RAL 7035 polyester powder coated.

Pack quantity: 1 kit of ground mounted plinth.

SPECIFICATIONS

Thickness:	2mm
Finish:	Galvanized
Material:	Galvanized Steel
Color:	Light Gray
Color Code:	RAL 7035

Table 1/1

Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Quick Ship
PGM10064	1000mm	600mm	400mm	Aluminum	Free-Standing	No
PGM10066	1000mm	600mm	600mm	Aluminum	Free-Standing	No
PGM10084	1000mm	800mm	400mm	Aluminum	Free-Standing	No
PGM10086	1000mm	800mm	600mm	Aluminum	Free-Standing	No
PGM10124	1000mm	1200mm	400mm	Aluminum	Free-Standing	No
PGM10126	1000mm	1200mm	600mm	Aluminum	Free-Standing	No
PGM10184	1000mm	1800mm	400mm	Aluminum	Free-Standing	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE