

Shelf 19-Inch, VSF



This shelf can be adjusted in height and provides further mounting possibilities with a higher loading capacity. It also has ventilation openings to ensure for proper air circulation within the enclosure.

FEATURES

Description: Maximum loading capacity when mounted directly onto the 19" profiles, front and rear. Ventilation openings.

Material: 1.5 mm steel.

Finish: RAL 7035.

Pack quantity: 1 shelf with mounting material.

Maximum load capacity: 1200 N

SPECIFICATIONS

- Thickness: 1.5mm
- Color: Light Gray
- Material: Mild Steel
- Finish: Powder Coated
- Color Code: RAL 7035

Table 1/1						
Catalog Number	Height	Width	Depth	Load Rating	Enclosure Material	Quick Ship
VSF1470	19mm	468mm	468mm	1200N	Mild Steel	No
VSF1406	19mm	404mm	404mm	1200N	Mild Steel	No
VSF1597	19mm	595mm	595mm	1200N	Mild Steel	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE