

# Varistar CP Steel Door, Plain With 3-Point Locking, IP55

## Power Utilities

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

### FEATURES

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Height  | Width  | Color      | Color Code | Complies With |
|----------------|-------------|---------|--------|------------|------------|---------------|
| 21630-171      | 47 U        | 2200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-210      | 24 U        | 1200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-211      | 29 U        | 1400 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-212      | 33 U        | 1600 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-213      | 38 U        | 1800 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-214      | 42 U        | 2000 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-215      | 47 U        | 2200 mm | 600 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-216      | 24 U        | 1200 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1   |

| CatalogNumber | Rack Height | Height  | Width  | Color      | Color Code | Complies With |
|---------------|-------------|---------|--------|------------|------------|---------------|
| 21630-217     | 29 U        | 1400 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-218     | 33 U        | 1600 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-219     | 38 U        | 1800 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1   |
| 21630-220     | 42 U        | 2000 mm | 800 mm | Black Grey | RAL 7021   | IEC 61587-1   |

Table 2/3

| Catalog Number | Finish        | Locking Type    | Material | Product Type | Protection Rating | Type       |
|----------------|---------------|-----------------|----------|--------------|-------------------|------------|
| 21630-171      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-210      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-211      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-212      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-213      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-214      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-215      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-216      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-217      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-218      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-219      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |
| 21630-220      | Powder Coated | 3-Point Locking | Steel    | Cabinet Door | IP55              | Steel Door |

Table 3/3

| Catalog Number | Works With  |
|----------------|-------------|
| 21630-171      | Varistar CP |
| 21630-210      | Varistar CP |
| 21630-211      | Varistar CP |
| 21630-212      | Varistar CP |
| 21630-213      | Varistar CP |
| 21630-214      | Varistar CP |
| 21630-215      | Varistar CP |
| 21630-216      | Varistar CP |
| 21630-217      | Varistar CP |
| 21630-218      | Varistar CP |
| 21630-219      | Varistar CP |
| 21630-220      | Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**