

nVent CADDY Quick Clip Rod Stiffener



FEATURES

Secures strut channel to threaded rod for stiffening

One hand, snap-in place installation

No tools or bolt tightening required

SPECIFICATIONS

Material: Stainless Steel 316 (EN 1.4401)

Table 1/1

Catalog Number	Article Number	Strut Type	Rod Size (RS)
CSBRS2	404538	A (41 x 41 mm)	10
CSBRS3	404539	A (41 x 41 mm)	12
CSBRS4	402532	A (41 x 41 mm)	16

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

