

Multi-Purpose Grounding Clamp, Galvanized Steel



FEATURES

Multi-purpose grounding clamp allows connection of round conductors, flat conductors, or rebar

Connecting plates can rotate, allowing connections at varying angles

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Material	Finish	Conductor Size	Tape Size	Rebar Size, Metric
CPD2440	101100	Steel	Electrogalvanized	50 mm ² Stranded, 2/0 Solid	40 x 5 mm Max	20 mm Max

Table 2/3

Catalog Number	Article Number	Rebar Size, US	Rebar Size, Canada	Length 1 (L1)	Length 2 (L2)	Width (W)
CPD2440	101100	#7 Max	20M Max	83 mm	30 mm	60 mm

Table 3/3

Catalog Number	Article Number	Torque (TQ)	Complies With
CPD2440	101100	35 N·m	IEC® EN 62561-1:2017 Class H

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE