

# CleanTray 45-Degree Elbow



Clean Tray 45-Degree Elbows are used for continuous runs with 45-degree turns. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

## FEATURES

---

Clean Tray 45-Degree Elbows are used for continuous runs with 45-degree turns

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

## SPECIFICATIONS

**Finish:** Brushed #3  
**Material:** Stainless Steel 304

Table 1/1

| Catalog Number | Type  | Height | Width | Thickness | Quick Ship |
|----------------|-------|--------|-------|-----------|------------|
| CT22EFC45SS    | Elbow | 51mm   | 51mm  | 1.27mm    | No         |
| CT33EFC45SS    | Elbow | 76mm   | 76mm  | 1.27mm    | No         |
| CT33EIC45SS    | Elbow | 76mm   | 76mm  | 1.27mm    | No         |
| CT33EOC45SS    | Elbow | 76mm   | 76mm  | 1.27mm    | No         |
| CT44EFC45SS    | Elbow | 102mm  | 102mm | 1.27mm    | No         |
| CT44EIC45SS    | Elbow | 102mm  | 102mm | 1.27mm    | No         |
| CT44EOC45SS    | Elbow | 102mm  | 102mm | 1.27mm    | No         |
| CT44PEFC45SS   | Elbow | 102mm  | 102mm | 1.27mm    | No         |
| CT46EFC45SS    | Elbow | 102mm  | 152mm | 1.27mm    | No         |
| CT46EIC45SS    | Elbow | 102mm  | 152mm | 1.27mm    | No         |
| CT46EOC45SS    | Elbow | 102mm  | 152mm | 1.27mm    | No         |
| CT66EFC45SS    | Elbow | 152mm  | 152mm | 1.27mm    | No         |
| CT66EOC45SS    | Elbow | 152mm  | 152mm | 1.27mm    | No         |
| CTS33EFC45SS   | Elbow | 76mm   | 76mm  | 1.27mm    | No         |
| CTS33PEFC45SS  | Elbow | 76mm   | 76mm  | 1.27mm    | No         |
| CTS44EFC45SS   | Elbow | 102mm  | 102mm | 1.27mm    | No         |
| CTS44PEFC45SS  | Elbow | 102mm  | 102mm | 1.27mm    | No         |

| Catalog Number | Type  | Height | Width | Thickness | Quick Ship |
|----------------|-------|--------|-------|-----------|------------|
| CTS46EFC45SS   | Elbow | 102mm  | 152mm | 1.27mm    | No         |
| CTS46PEFC45SS  | Elbow | 102mm  | 152mm | 1.27mm    | No         |
| CTS66EFC45SS   | Elbow | 152mm  | 152mm | 1.27mm    | No         |
| CTS66PEFC45SS  | Elbow | 152mm  | 152mm | 1.27mm    | No         |
| CT22EIC45SS    | Elbow | 51mm   | 51mm  | 1.27mm    | No         |
| CT22EOC45SS    | Elbow | 51mm   | 51mm  | 1.27mm    | No         |
| CT22PEFC45SS   | Elbow | 51mm   | 51mm  | 1.27mm    | No         |
| CT33PEFC45SS   | Elbow | 76mm   | 76mm  | 1.27mm    | No         |
| CT46PEFC45SS   | Elbow | 102mm  | 152mm | 1.27mm    | No         |
| CT66EIC45SS    | Elbow | 152mm  | 152mm | 1.27mm    | No         |
| CT66PEFC45SS   | Elbow | 152mm  | 152mm | 1.27mm    | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**