

# Connection Terminal Plate, W060



Connection terminal plate for many different conductor types.

## INDUSTRY STANDARDS

---

UL

CSA

GL

## FEATURES

---

Description: Connection terminal plate, 3-pole, with cover cap.

For busbars: 12, 15, 20, 25, 30 × 5, 10.

Rated voltage: 690 V

Rated peak withstand current I<sub>pk</sub> max: 40.5 kA (01240), 56.3 kA (01243)

Pack quantity: 1 pc.

Approvals: CSA, UL, GL

SPECIFICATIONS

| Table 1/1      |        |       |       |          |          |            |
|----------------|--------|-------|-------|----------|----------|------------|
| Catalog Number | Height | Width | Depth | Material | Finish   | Color      |
| 01240          | 54mm   | 25mm  | 32mm  | Plastic  | Textured | Light Gray |
| 01243          | 81mm   | 25mm  | 32mm  | Plastic  | Textured | Light Gray |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE