

Gland Plate Gaskets, AG



The polyethylene gasket will guarantee that the enclosure's protection degree is maintained to protect components and equipment installed within it.

FEATURES

Description: For standard gland plate opening.

Material: 4 mm polyethylene foam.

Pack quantity: 1 piece.

SPECIFICATIONS

Height:	4mm
Thickness:	4mm
Color:	Black
Material:	Polyethylene Foam
Finish:	Smooth Matte

Table 1/1

Catalog Number	Width	Depth	Gland Plate Type	Gland Plate Opening Width	Gland Plate Opening Depth	Enclosure Material
AG00S	140mm	86mm	0S	110mm	56mm	Mild Steel
AG01	240mm	126mm	1	210mm	96mm	Mild Steel
AG01S	240mm	86mm	1S	210mm	56mm	Mild Steel
AG02	340mm	126mm	2	310mm	96mm	Mild Steel
AG02S	340mm	86mm	2S	310mm	56mm	Mild Steel
AG03	440mm	126mm	3	410mm	96mm	Mild Steel
AG03S	440mm	86mm	3S	410mm	56mm	Mild Steel
AG04	540mm	126mm	4	510mm	96mm	Mild Steel

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE