

# 19" Fan Unit, 1 U

## Power Utilities

Fan Unit for installation into a 1U space within the Cabinet.



### CERTIFICATIONS



### FEATURES

Mechanical strain relief for mains cables

Can be adapted to sub racks

Contact protection in accordance with DIN EN ISO 13857

### SPECIFICATIONS

Table 1/1

| Catalog Number | Input Voltage AC | Input Voltage DC |
|----------------|------------------|------------------|
| 10713-104      | 230 V min        |                  |
| 10713-100      | 230 V min        |                  |
| 10713-106      | 115 V min        |                  |

| Catalog Number | Input Voltage AC | Input Voltage DC |
|----------------|------------------|------------------|
| 10713-102      | 115 V min        |                  |
| 10713-103      |                  | 24 V min         |
| 10713-107      |                  | 24 V min         |

## ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

Wide-range input voltage (86 ... 264 VAC) available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**