

Varistar CP Steel Door, Plain With 3-Point Locking and Brush Strip, Shortened

Power Utilities

Shortened door available for IP20, IP55 applications.

FEATURES

Height of connection plate 400 mm

Connection plate with brush strip

The height of the door is 400 mm less than the cabinet height

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Locking Type
21630-352	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-348	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-351	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-350	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-353	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-349	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Catalog Number	Product Type	Protection Rating
----------------	--------------	-------------------

21630-352	Cabinet Door	IP20
21630-348	Cabinet Door	IP20
21630-351	Cabinet Door	IP20
21630-350	Cabinet Door	IP20
21630-353	Cabinet Door	IP20
21630-349	Cabinet Door	IP20

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE