

Intelligent iPDU, EN6450, 400 VAC, 3-PH, 16 A

CATALOG NUMBER

EN6450



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

FEATURES

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Intelligent PDU

Product Type: Socket Strip

Socket Type: (24) C13/C15; (24) C13/C15/C19/C21

Socket Quantity: 48

Color: Black

Circuit Breaker: No Circuit Breaker

Switched Outlets: Yes

Circuit Breaker Quantity: 0

Power Rating: 11.5 kVA North America; 11.0 kVA International

Input Cable Location: Top Feed

Max Power Input: 11.5 / 11.0 kVA

Input Voltage: 380 – 415V

Phase: 3 PH

On/Off Switch Included: Yes

Nominal Voltage: 415V

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 520P6/516P6

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Removable Input Cable: No

Rack Units: 0U

Material: Steel

Finish: Powder Coated

Metering Type: Outlet

Height: 1490mm

Width: 56mm

Depth: 75mm

Weight: 12kg

Package Quantity: 1

Input Cable Length: 1.8m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE