


# Varistar CP Air Separation Blanking Cover, Width 800 mm, With Brush Strip and Fingers



Filler panel for 800 mm wide cabinets to avoid air recirculation in front to back cooled racks. Plain panels and panels with cutouts for front to back cabling with brush stripes and cable fingers.

## FEATURES

Air separation, covers for 800 mm wide cabinets

Network and server cabinets can be arranged side by side

Gaskets, UL 94 HF-1, -20 °C ... 100° C

Cover with cutouts and cable fingers for efficient cable management

Brush strips available to close the cutouts

Covers prevent unwanted air short-circuits, i.e. unwanted mixing of warm exhaust air with cold inbound air

Only compatible with heavy load crossbar, not compatible with reduction brackets

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Panel

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Package Quantity | Color      | Color Code | Finish        |
|----------------|-------------|--------|------------------|------------|------------|---------------|
| 21630-150      | 42U         | 2000mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-152      | 52U         | 2450mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 21630-151      | 47U         | 2200mm | 1                | Black Grey | RAL 7021   | Powder Coated |

Table 2/2

| Catalog Number | Protection Rating | Type       | Width | Quick Ship |
|----------------|-------------------|------------|-------|------------|
| 21630-150      | IP20              | Cable Duct | 800mm | No         |
| 21630-152      | IP20              | Cable Duct | 800mm | No         |
| 21630-151      | IP20              | Cable Duct | 800mm | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**