

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

SPECIFICATIONS

Product Type: Cabinet
Cladding Color Code: RAL 7021
Frame Material: Steel

Table 1/3

Catalog Number	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-036	42U	2000mm	Black Grey	600mm	RAL 7021	Steel
10630-035	42U	2000mm	Black Grey	600mm	RAL 7021	Steel

CatalogNumber	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-033	38U	1800mm	Black Grey	600mm	RAL 7021	Steel
10630-034	38U	1800mm	Black Grey	600mm	RAL 7021	Steel

Table 2/3

Catalog Number	Depth	Cladding Color	Package Quantity	Complies With	Finish	Material
10630-036	800mm	Black Grey	1	IEC 60297-3-100	Powder Coated	Steel
10630-035	600mm	Black Grey	1	IEC 60297-3-100	Powder Coated	Steel
10630-033	600mm	Black Grey	1	IEC 60297-3-100	Powder Coated	Steel
10630-034	800mm	Black Grey	1	IEC 60297-3-100	Powder Coated	Steel

Table 3/3

Catalog Number	Static Load	Quick Ship
10630-036	400kg	No
10630-035	400kg	No
10630-033	400kg	No
10630-034	400kg	No

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE