

EBC Beam Clamp



CERTIFICATIONS



FEATURES

Easy installation to beam flanges

One 10.5mm go-through hole allows the use of M6, M8 or M10 threaded rod, to attach any static load till 450N

Featuring three M6 threaded holes to attach electrical boxes directly to the side or bottom of the beam

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Rod Size (RS)	Hole Size (HS)	Flange Thickness (FT)
EBC	170380	Spring Steel	nVent CADDY Armour	6	10.5 mm	16 mm Max

Table 2/2

Catalog Number	Article Number	Torque (TQ)	Static Load
EBC	170380	20 N·m	450N

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

