We connect and protect

Basic PDU, EB0401, 400 VAC, 3-PH, 16 A

Data Solutions

CATALOG NUMBER

EB0401

Modular, compact PDU. Ultra-Low Profile Design

FEATURES

- Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures
- Input Voltage 400 VAC, 3-phase
- C13 and C19 outlets
- 1RU aluminum profile
- Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

- Product Family: Enlogic
- Type: Basic PDU
- Product Type: Socket Strip
- Socket Type: (6) C19
- Socket Quantity: 6
- Color: Black
- Circuit Breaker: 16 A, 1-pole, Hy-Mag
- Switched Outlets: No

Circuit Breaker Quantity: 0

Input Cable Length: 3m

Input Cable Location: Top Feed

Input Voltage: 400V

Phase: 3 PH WYE

Interrupt Rating: 5kAIC

Max Power Input: 11.0 kVA

Amperage (Derated Amperage): 16 A

Output Voltage: 200 – 240VAC

Rack Units: 0U

Plug Type: IEC 60309 516P6 (IP44)

Metering Type: None

Removable Input Cable: No

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.