

Air Terminal Base, Stamped, Metric Thread



FEATURES

Unique design accepts multiple air terminal thread sizes

Less screws than typical bases allows for faster installation

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Thread Size (TS)	Tape Size	Depth (D)	Height (H)	Width (W)
ATBAS253	Aluminum	M10, M16	25 x 3 mm, 26 x 2 mm	57.4mm	40 mm	60 mm
ATBSS253	Stainless Steel 304 (EN 1.4301)	M10, M16	25 x 3 mm, 26 x 2 mm	57.4mm	40 mm	60 mm
ATBCS253	Copper	M10, M16	25 x 3 mm, 26 x 2 mm	57.4mm	40 mm	60 mm

Table 2/2

Catalog Number	Unit Weight
ATBAS253	0.09 kg
ATBSS253	0.13 kg
ATBCS253	0.13 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE