

Copper-Bonded Ground Rod, One Pigtail



The nVent ERICO Copper-Bonded Ground Rod, One Pigtail features a Cadweld exothermic connection that attaches the pigtail to the rod with a permanent, molecular bond that will not loosen or corrode. The pigtail has a thick copper coating for durability and conductivity. The rod undergoes a unique manufacturing process resulting in a straighter, stronger core that makes installation easier. The rod also has a uniform layer of molecularly bonded copper that provides long-lasting corrosion resistance. The Cadweld exothermic connection and the Copper-Bonded Ground Rod are designed to maintain for the life of the conductor and/or installation and can withstand repeated fault currents without failing.

FEATURES

Pigtails are connected with an exothermic Cadweld connection to rod

99.9% pure electrolytic copper coating

Manufactured in an ISO-registered manufacturing facility

Rods have a high carbon steel core and tip that provide superior strength when driving

SPECIFICATIONS

Material: Copper-Bonded Steel

Tensile Strength: 552 MPa Min

Table 1/2

Catalog Number	Ground Rod Diameter, Actual (Ø)	Length 1 (L1)	Length 2 (L2)	Plating Thickness	Cable Length	Conductor Size
6138529	8.9 mm	1524 mm Min	457 mm Min	127µm	0.45m	#10 CW
6138629	8.9 mm	1829 mm Min	457 mm Min	127µm	0.46m	#10 CW

CatalogNumber	Ground Rod Diameter, Actual (Ø)	Length 1 (L1)	Length 2 (L2)	Plating Thickness	Cable Length	Conductor Size
6158839	14.2 mm	2438 mm Min	1219 mm Min	330µm	1.2m	#6 Solid Copper
615889	14.2 mm	2438 mm Min	1219 mm Min	254µm	1.2m	#6 CW


Table 2/2

Catalog Number	Insulated	Unit Weight
6138529	No	0.7 kg
6138629	No	0.9 kg
6158839	No	3.1 kg
615889	No	3.1 kg

ADDITIONAL PRODUCT DETAILS

Contact us for specific requirements.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including nickel, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY	ERICO	HOFFMAN	ILSCO	SCHROFF	TRACHTE
-------	-------	---------	-------	---------	---------