


Rail Jumper Bond Kit, Signal, XS Style



FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

XS style bond end terminals are tinned to prevent contamination prior to installation

Easy installation, with minimum installer training required

Simple and highly-portable installation equipment

Equally usable on old, worn, or new rails

Highly durable

SPECIFICATIONS

Finish:	Bare;Tinned
Material:	Cadmium Bronze;Copper
Bond Terminal Style:	XS

Table 1/1


Catalog Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SBXSJ3312	3/16" Bondstrand	304.8 mm	19.05 mm	4.8 mm
SBXSJ3318	3/16" Bondstrand	457.2 mm	19.05 mm	4.8 mm
SBXSJ3324	3/16" Bondstrand	609.6 mm	19.05 mm	4.8 mm

Catalog Number	Conductor Size	Length 1 (L1)	Length 2 (L2)	Diameter (Ø)
SBXSJ3330	3/16" Bondstrand	762 mm	19.05 mm	4.8 mm
SBXSJ3332	3/16" Bondstrand	812.8 mm	19.05 mm	4.8 mm
SBXSJ3334	3/16" Bondstrand	863.6 mm	19.05 mm	4.8 mm
SBXSJ3336	3/16" Bondstrand	914.4 mm	19.05 mm	4.8 mm
SBXSJ3342	3/16" Bondstrand	1066.8 mm	19.05 mm	4.8 mm
SBXSJ3348	3/16" Bondstrand	1219.2 mm	19.05 mm	4.8 mm

ADDITIONAL PRODUCT DETAILS

Kits include: (25) bonds and (50) F80 alloy welding material.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including cadmium, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE