

Replacement Module for UTB, Single Pair Isolated Ground



CERTIFICATIONS



FEATURES

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions


Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring

SPECIFICATIONS

Catalog Number	UTB60SPGM	UTB5SPGM	UTB110SPGM	UTB30SPGM	UTB15SPGM
Article Number	702883	702879	702884	702882	702881
Nominal System Voltage (Un)	21 - 42 VAC 30 - 60 VDC	0 - 3 VAC 0 - 5 VDC	100 - 120 VAC 60 - 154 VDC	10 - 21 VAC 15 - 30 VDC	3 - 10 VAC 5 - 15 VDC
Max Continuous Operating Voltage (Uc)	45 VAC 64 VDC	5 VAC 7 VDC	150 VAC 170 VDC	23 VAC 33 VDC	12 VAC 18 VDC

Catalog Number	UTB60SPGM	UTB5SPGM	UTB110SPGM	UTB30SPGM	UTB15SPGM
Rated Load Current (IL)	2A	2A	2A	2A	2A
Frequency	3 MHz	0.5 MHz	3 MHz	2 MHz	1 MHz
Loop Resistance	1 Ω	1 Ω	1 Ω	1 Ω	1 Ω
Max Discharge Current (Imax), L+L-PE	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s	20kA 8/20 μ s
Protection Modes	Common Differential	Common Differential	Common Differential	Common Differential	Common Differential
Technology	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)
Voltage Protection Level (Up), L-L	85 V @ 3 kA	10 V @ 3 kA	220 V @ 3 kA	44 V @ 3 kA	25 V @ 3 kA
Temperature	-20 to 65 $^{\circ}$ C	-20 to 65 $^{\circ}$ C	-20 to 65 $^{\circ}$ C	-20 to 65 $^{\circ}$ C	-20 to 65 $^{\circ}$ C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Depth (D)	52mm	52mm	52mm	52mm	52mm
Height (H)	43 mm	43 mm	43 mm	43 mm	43 mm
Width (W)	12 mm	12 mm	12 mm	12 mm	12 mm
Unit Weight	0.02 kg	0.02 kg	0.02 kg	0.02 kg	0.02 kg
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE